

Extract of the stocklist

Material	mesh	Mode of weaving	aperture in micron ca.	wire diameter in mm
4301	12/64	plain dutch	300	0,60/0,40
4301	14/88	plain dutch	200	0,50/0,32
4301	24/110	plain dutch	150	0,35/0,25
4301	30/150	plain dutch	100	0,23/0,18
4301	40/200	plain dutch	80	0,18/0,14
4301	50/250	plain dutch	60	0,14/0,11
4301	80/300	plain dutch	40	0,12/0,09
4401	12/64	plain dutch	300	0,60/0,40
4401	24/110	plain dutch	150	0,35/0,25
4401	30/150	plain dutch	100	0,23/0,18
4401	40/200	plain dutch	80	0,18/0,14
4401	50/250	plain dutch	60	0,14/0,11
4401	80/300	plain dutch	40	0,12/0,09
4401	80/400	plain dutch	40	0,125/0,071
FE	12/64	plain dutch	300	0,60/0,40
FE	14/88	plain dutch	200	0,50/0,32
FE	24/110	plain dutch	150	0,35/0,25
FE	30/150	plain dutch	100	0,23/0,18

Other designs on request



Extract of the stocklist

Material	mesh	Mode of weaving	aperture in micron ca.	wire diameter in mm
4401	028/268	plain dutch	84	0,34/0,102
4401	030/280	plain dutch	90	0,28/0,10
4401	040/340	plain dutch	78	0,23/0,08
4401	050/400	plain dutch	60	0,16/0,07
4401	060/490	plain dutch	48	0,16/0,058
4401	080/700	plain dutch	34	0,13/0,04
4401	120/930	plain dutch	25	0,065/0,03

Other designs on request